




|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | PLUS handrail section 1200 mm.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Item number</b>         | RT303112                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Colour</b>              | <p>VVS:777569032<br/>NRF:6311248<br/>EAN:5708590318837<br/>NBS:N13:436</p> <p>Anthracite grey</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Product description</b> | <p>RT300 - A = 300<br/>RT303 - A = 1200<br/>RT307 - A = 2400</p>  <p>PLUS hand rail tube.<br/>Length 1200 mm, diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube.<br/>Length 1200 mm, diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.<br/>Materials: Powder-coated aluminium.</p> |
| <b>Product capacity</b>    | <p>Maximum load: With a span up to 1000 mm: 210 kg<br/>With a span up to 1300 mm: 150 kg.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>Materials</b>           | <p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Ergonomy</b>            | <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Warranty</b>            | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Cleaning</b>            | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |



# PRESSALIT®

|                    |                                |
|--------------------|--------------------------------|
| <b>Product</b>     | PLUS handrail section 1200 mm. |
| <b>Item number</b> | RT303112                       |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®

8. juli 2026