




Product Item number	MATRIX supports for wash basin, 200 mm height adjustable R2015182
Colour	VVS:636858810 NRF:6132552 EAN:5708590329345 HMI: 106240 NBS:N13:30,335 FDA:ILW/D142473 Pale grey
Product description	 MATRIX supports are the low cost solution for MATRIX MEDIUM and ANGLE wash basins. They are available in a manually height adjustable version, which is suitable for infrequent adjustment. Wash basin brackets, set of 2 pcs. 200 mm height adjustable (Not for frequent adjustment). Suitable for MEDIUM and ANGLE wash basins with integrated handrails. Recommendation: Flexible feed and waste system R2067/R2065. (UK markets R2077/R2075). Excl. mounting kit.
Adjustability Adjustment height Product capacity	Height adjustable 200 mm Maximum user weight (MUM): 160 kg. Maximum load (SWL): 150 kg. Suitable for wash basins weighing no more than 30 kg. When the wash basin is loaded with 150 kg, each wall fastener will be carrying 30 kg. <i>Wash basin brackets need to be able to carry the weight of the wash basin, as well as support the weight of the person who is leaning against the wash basin or who is using the wash basin to rise from seated position.</i> Neither wash basin nor wash basin bracket are intended to carry the full body weight of a person, and the test methods applicable to wash basin brackets reflect this: ISO 17966 prescribes a static test on the front edge of the wash basin at 75% of maximum user weight, i.e. when the maximum load on a wash basin bracket is given as 150 kg and the wash basin weighs 30 kg, it is – according to ISO 17966 – the equivalent of a user weighing 160 kg leaning on the front edge of the wash basin.



PRESSALIT®





Product	MATRIX supports for wash basin, 200 mm height adjustable
Item number	R2015182
Materials	Powder coated steel
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged. For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättspit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.





PRESSALIT®

Product	MATRIX supports for wash basin, 200 mm height adjustable
Item number	R2015182

Installation in different wall types

	Concrete >B25 V8601 - Mounting kit, 8 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Solid Brick >= Mz12 V8601 - Mounting kit, 8 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8601 - Mounting kit, 8 coach screws Ø6 x 70 - plugs SX8. To be ordered separately.	
	Aerated Concrete P4 It is not recommended to install this product in aerated concrete.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8601 - Mounting kit, 8 coach screws Ø6 x 70 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



Product Item number	MATRIX supports for wash basin, 200 mm height adjustable R2015182	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	

It is the responsibility of the installer to ensure that suitable wall fasteners are used.