




Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout R8683000
Colour Product description	<p>VVS: 777636230 NRF: 7501982 RSK: 8565117 EAN: 5708590338422 HMI: 48576 White</p>  <p>Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves. All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads.</p> <p>Low start, wallhung changing table, with sanitary appliances, 800 x 1800 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control and safety stop function. Laminate worktop with inset stainless steel sink, incl. lever operated mixer tap, pull-out shower head, feed/waste system and 2 wire baskets. Materials: Laminate and powder-lacquered steel. Excl. mounting kit.</p>
Adjustability Adjustment height Product capacity Speed upwards Noise level	Height adjustable 700 mm Max load: 75 kg. Speed up mm: 38 mm/s Speed down mm: 38 mm/s 48 dB



Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Item number	R8683000
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: Melamine. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.
Features	Easy-to-clean surfaces ensure optimum hygiene. Underglued sink and tap with pull-out spout. Integrated safety system prevents entrapment.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 3500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Item number	R8683000
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.








Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Item number	R8683000

Installation in different wall types

	<p>Concrete >B25 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Aerated Concrete P4 V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p>	



Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout R8683000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 