




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                          |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS shower head holder<br>RT600000                                                                                                                                                                                                                      |
| <b>Colour</b>                        | VVS:777564700<br>NRF:6191674<br>RSK:8180966<br>EAN:5708590169965<br>HMI: 42227<br>NBS:N13:40,375<br>White                                                                                                                                                |
| <b>Product description</b>           | <br>Shower head holder recommended with hand rails RT118/119, RT136/138 or RT144.<br>Shower head holder recommended with hand rails RT118/119, RT136/138 eller RT144. |
| <b>Materials</b>                     | Polycarbonate (PC) and ABS plastic                                                                                                                                                                                                                       |
| <b>Ergonomy</b>                      | Easy height adjustment with one hand or hands with little strength.                                                                                                                                                                                      |
| <b>Features</b>                      | For mounting on handrails with a diameter of 33 mm.                                                                                                                                                                                                      |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                            |
| <b>Cleaning</b>                      | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                               |



# PRESSALIT®

|                    |                         |
|--------------------|-------------------------|
| <b>Product</b>     | PLUS shower head holder |
| <b>Item number</b> | RT600000                |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®

8. juli 2026