




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Choice Toilet brush for wall, brushed brass<br>Q70850                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Product description</b>           | <p>VVS:778497205<br/>NRF:7001083<br/>RSK:8714275<br/>EAN:5708590372242<br/>DB: 2173273</p>  <p>Let the Pressalit Choice bathroom accessory series elevate the décor of your bathroom and create coherence with a timeless look. You get a complete range of accessories to suit any bathroom.</p> <p>Elegant toilet brush for wall mounting. Opens up extra space on the floor.</p> |
| <b>Materials</b>                     | Stainless steel AISI 304, mounting knot in brass                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                  |

[pressalit.com](http://pressalit.com)