



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Choice Towel hook, 2 pcs., brushed brass<br>Q70100                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Product description</b>           | <p>VVS:775295105<br/>NRF:7001076<br/>RSK:8755024<br/>EAN:5708590372181<br/>DB: 2173267</p>  <p>Let the Pressalit Choice bathroom accessory series elevate the décor of your bathroom and create coherence with a timeless look. You get a complete range of accessories to suit any bathroom</p> <p>Use the towel hook in the bathroom and in the kitchen. That way, you can let the style be consistent throughout the house.</p> |
| <b>Materials</b>                     | Stainless steel AISI 304, mounting knot in brass                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                                                                 |

[pressalit.com](http://pressalit.com)