



<b>Product</b> <b>Item number</b>	Pressalit Public Premium Hand dryer with sensor, brushed steel PX30515
<b>Product description</b>	VVS:776133315 NRF:1438621 RSK:8865104 EAN:5708590395517  Stainless steel warm air hand dryer for wall mounting. Low-noise fan with sensor activated at 172mm (± 20 mm). Drying time approx. 15 sec. Connection for fixed installation or installation via circuit breaker. Permanent installation must be carried out by an authorized electrician  Power 840-1000 W. 230 V / 50/60 Hz
<b>Materials</b>	European stainless steel (AISI 304)
<b>Warranty</b>	A 2-year warranty is provided for material and manufacturing defects.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
<b>WEEE</b>	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.  Subject to changes in the product range, technical changes and printing errors.



PRESSALIT®

<b>Product</b>	Pressalit Public Premium Hand dryer with sensor, brushed steel
<b>Item number</b>	PX30515

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®