




| | |
|--------------------------------------|--|
| Product Item number | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm RT138000 |
| Colour | VVS:777568700 NRF:6311233 RSK:8980588 EAN:5708590146492 HMI: 25429 NBS:N13:436 FDA:ILS/D135866 White |
| Product description |  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail combination, 33 mm, reversible right/left, A: 762 mm x B: 1200 mm x C: 1090 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic Excl. mounting kit.</p> |
| Product capacity | Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i> |
| Materials | Basic material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclooy plastic Strap: Nylon (PA) |
| Ergonomy | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail. |



| | |
|--------------------|--|
| Product | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm |
| Item number | RT138000 |
| Warranty | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. |
| Cleaning | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |









| | |
|--------------------|--|
| Product | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm |
| Item number | RT138000 |

Installation in different wall types

| | | |
|--|--|--|
| | <p>Concrete >B25 V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> | |
| | <p>Solid Brick >= Mz12 V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> | |
| | <p>Solid Sand Lime Brick >= Hlz12 V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> | |
| | <p>Aerated Concrete P4 V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p> | |
| | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> | |



| | |
|---|--|
| Product Item number | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm RT138000 |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.  |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.  |
|  | Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.  |