




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Paper dispenser, manual, 300 sheets, brushed steel<br>PX30105                                                                                                                                                                                                                                                                                                                                             |
| <b>Product description</b>           | <p>VVS: 776130315<br/>NRF: 1438630<br/>RSK: 8920364<br/>EAN: 5708590392134</p>  <p>Stainless steel paper dispenser for wall mounting. Open top with visible brushed steel surface. Holds approx. 300 sheets of paper. Incl. mounting kit.</p> <p>There is an inspection opening to indicate filling level and filling is done from the top.</p> |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                              |

[pressalit.com](http://pressalit.com)