




PRESSALIT®

Product Item number	Flexible feed and waste system 36"/36" R2087
Product description	EAN: 5708590360461  The flexible feed and waste systems are needed to ensure the flow of water to and from the height adjustable sink brackets. Flexible feed/waste system. Feed pipes: 36", waste pipe: 36". tap supply line braided stainless steel, with 3/8". OD x 1/2". IPS x 16". Flexible waste pipe, dia. 1.26".
Materials	The feed pipes are made from SPX plastic, braided with stainless steel. The connecting nuts are 3/8" and made from brass with 3/8" copper pipe. The waste pipe is flexible, corrugated white PVC with a diameter of 1.3". We do not recommend flushing the waste hose with formaldehyde. The elbow with removable connector is made from PP (polypropylene) with a seal of TPE (thermoplastic elastomer). Maximum temperatures of use are 176°F (continuous use) and 194°F (temporary use). PP is very resistant to water, damp and most organic solvents. The seal is made from EPDM – Temperature of use from -58°F - +248°F/305°F EPDM is particularly resistant to ozone and weather. Good resistance to heat and cold and to most chemicals – but poor resistance to petroleum products and solvents.
Ergonomy	To maximize product flexibility, it is important that the plumbing installation is correctly positioned and does not obstruct movement. The waste hose can be shortened on site to fit the installation.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	When cleaning the sink, it is recommended to do one flush through the waste hose with 122-140 degrees hot water in order to prevent build-up of soap residues inside the hose. Ensure that the hose is stretched out during this flushing.



PRESSALIT®

Product	Flexible feed and waste system 36"/36"
Item number	R2087

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®