




<p>Product Item number</p>	<p>PLUS sink bracket with lever control, electrically height adjustable R4750-93</p>
<p>Product description</p>	<p>EAN:5708590316109 FDA:ILW/D142473</p>  <p>PLUS sink brackets are available in electrically, pneumatically and manually height adjustable versions. They are suitable for wall-mounting or for fitting to Pressalit PLUS wall tracks.</p> <p>PLUS sink bracket, wall-mounted. Electrically height adjustable by 11.8" with lever control. Lever control is placed at the front of the sink, it can be used as a towel bar and can be placed on either side of the sink. Recommendation: flexible feed/waste system R2085/R2087. Incl. mounting bolts for sink (Recommended with MATRIX SMALL and MATRIX CURVE/NEW CURVE sinks). Materials: Aluminium and ABS polymer. Excl. mounting kit.</p>
<p>Adjustability</p>	<p>Height adjustable</p>
<p>Adjustment height</p>	<p>11,82 inch</p>
<p>Product capacity</p>	<p>Maximum load: 220 lbs. Suitable for sinks weighing no more than 49 lbs. When the sink is loaded with 220 lbs, each wall fastener will be carrying 93 lbs. <i>Sink brackets need to be able to carry the weight of the sink, as well as support the weight of the person who is leaning against the sink or who is using the sink to rise from seated position.</i> Neither sink nor sink bracket are intended to carry the full body weight of a person, and the test methods applicable to sink brackets reflect this: ISO 17966 prescribes a static test on the front edge of the sink at 75% of maximum user weight, i.e. when the maximum load on a sink bracket is given as 220 lbs and the wash basin weighs 49 lbs, it is – according to ISO 17966 – the equivalent of a user weighing 229 lbs leaning on the front edge of the wash basin.</p>



Product	PLUS sink bracket with lever control, electrically height adjustable
Item number	R4750-93
Speed up	Speed up: 0,79 inch/s Speed down: 0,91 inch/s
Noise level	45 dB
Materials	The sink bracket is primarily made of 3/8" anodized aluminium. The ends of the bracket cover are capped with ABS polymer. The bracket is available with a lever control consisting of an ABS polymer switch at the end of an anodized aluminium arm
Ergonomy	The height of the sink is easily adjusted the lever control. The sink bracket is compatible with all types of bolt-mounted sink. It's rounded, sleek design makes it easy to clean thoroughly.
Features	The arm that holds the lever control can function as a towel bar. The lever control can be placed on the right- or left-hand side of the sink. The user can easily make height adjustments independently using the electrically operated sink bracket.
Mains connection (V)	120
Actuator (motor)	LA40 (Linak) 4000N, IPX6
Control box	SMPS14002
Power consumption (maximum load)	Power consumption by maximum load: 75 W Power consumption by standby: 1,5 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.













Product	PLUS sink bracket with lever control, electrically height adjustable
Item number	R4750-93
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>
WEEE	<p>Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.</p> <p>Pressalit A/S, Pressalitvej 1, 8680 Ry, Denmark</p>








Product	PLUS sink bracket with lever control, electrically height adjustable
Item number	R4750-93

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8603 - Mounting kit, 4 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8603 - Mounting kit, 4 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8603 - Mounting kit, 4 lag bolts Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8653 - Mounting kit, 4 bolts M8 x 35, plugs FTP M 8. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8603 - Mounting kit, 4 lag bolts Ø8 x 70, plugs SX10. NB! Plugs are not needed. To be ordered separately.</p>	



Product Item number	PLUS sink bracket with lever control, electrically height adjustable R4750-93	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	Drywall (2 x 12,5 mm) water-resistant Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	