



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                               |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Classic Disinfection dispenser with sensor, 700 ml, matt black<br><br>PY40725                                                                                                                                                                                                                                                |
| <b>Product description</b>           | VVS: 774565631<br>NRF: 1438615<br>RSK: 8920399<br>EAN: 5708590392769<br><br>Disinfection dispenser with stainless steel sensor for wall mounting. One-handed disinfection pump with 700 ml tank. Designed for standard hand sanitizers. Lockable solution. Including mounting kit.<br><br>Inspection opening indicates filling level.         |
| <b>Materials</b>                     | European stainless steel (AISI 316L)                                                                                                                                                                                                                                                                                                          |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors. |

[pressalit.com](http://pressalit.com)