




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS handrail corner shower combination, reversible left/right, 762 x 762 x 1250 mm<br>RT156112                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Colour</b>                        | VVS: 777568682<br>NRF: 6317194<br>EAN: 5708590371146<br>HMI: 125873<br>FDA: ILS/D135866<br>Anthracite grey                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Product description</b>           |  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail combination, 33 mm, reversible right/left, A: 762 mm x B: 762 mm x C: 1250 mm, for fixed mounting.<br/> The projection of 50 mm from the wall makes it easy to take hold of the rail.<br/> Inkl. wall rosette, which covers the fixings.<br/> Material: Powder-coated aluminium and plastic.<br/> Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: 235 kg.<br>When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.<br><i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Materials</b>                     | Basic material: Aluminium<br><br>Surface material: Polyester lacquer<br><br>Cover cap: Cyclopy plastic<br><br>Strap: Nylon (PA)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Ergonomy</b>                      | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |



|                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS handrail corner shower combination, reversible left/right, 762 x 762 x 1250 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Item number</b> | RT156112                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Cleaning</b>    | <p>Handrails ALU</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningssprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |



PRESSALIT®





|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS handrail corner shower combination, reversible left/right, 762 x 762 x 1250 mm |
| <b>Item number</b> | RT156112                                                                            |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                                                                                                       |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | <b>Concrete &gt;B25</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                        |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                  |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                     |
|  | <b>Aerated Concrete P4</b><br>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.                                                                  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.  |



# PRESSALIT®

|                                                                                     |                                                                                                                                                                                                                                                                                                                |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b>                                                | PLUS handrail corner shower combination, reversible left/right, 762 x 762 x 1250 mm<br>RT156112                                                                                                                                                                                                                |
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>        |
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>                                                                     |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®