



PRESSALIT®

Product Item number	Pressalit Public Premium Power supply, C 3 volt, suitable for dispensers with infrared sensor PX00789
Product description	VVS: 774565989 NRF: 1438637 RSK: 8920356 EAN: 5708590392059 Power supply for infrared sensor module. Can be used as a regular power supply from a wall outlet with the module instead of batteries. Cable length 1.35 m. Primary: 100V-240V~, 50/60 Hz, 0.5A. Secondary: 3V=, 2A.
Warranty Cleaning	A 2-year warranty is provided for material and manufacturing defects. This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. Subject to changes in the product range, technical changes and printing errors.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®