




|   |  |
|---|--|
| <p><b>Product</b><br/><b>Item number</b></p>                              | <p>TMA 2 arm support for mounting on toilet, wider fit<br/>R1191112000</p>   |
| <p><b>Color</b><br/><br/><b>Product description</b></p>                   | <p>VVS:615724100<br/>NRF:6190325<br/>EAN:5708590376240<br/>HMI: 130727<br/>DB: 2510918<br/>FDA:ILS/D135866<br/>White</p>  <p>TMA arm supports comes in various widths, and models with or without toilet seat.</p> <p>TMA 2 arm supports for mounting on toilet, incl. BL1999 hinge. Dark gray handles. BL1 hinge, is only recommended with toilet seats R26, R27, R28, R29, R37 or R38.</p>  |
| <p><b>Adjustability</b></p>   | <p>Fixed mounting</p>  |
| <p><b>Materials</b><br/><br/><b>Ergonomy</b><br/><br/><b>Features</b></p> | <p>Powder-coated stainless steel.<br/>Soft polyurethane.<br/><i>Flammability-tested (ISO 8191-1). Test report available.</i></p> <p>The arm supports provide firm support and the molded handles are comfortable to hold on to.</p> <p>The arm supports can be folded individually.</p>  |
| <p><b>Warranty</b><br/><br/><b>Cleaning</b></p>                           | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> <p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> |



PRESSALIT®

|                    |   |
|--------------------|---|
| <b>Product</b>     | TMA 2 arm support for mounting on toilet, wider fit |
| <b>Item number</b> | R1191112000   |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®