



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Toilet paper holder with space for 5 rolls of toilet paper, matte black<br>PX40220                                                                                                                                                                                                                                                                  |
| <b>Product description</b>           | VVS: 776130531<br>NRF: 1438653<br>RSK: 8920375<br>EAN: 5708590392707<br><br>Stainless steel toilet paper holder with space for storing 5 rolls. For wall mounting. Designed for one standard toilet roll and four hidden rolls that automatically drop down. Including mounting kit.<br><br>Inspection opening to indicate filling level. Refill through opening in the top. |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                          |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors.                                |

[pressalit.com](http://pressalit.com)