




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Built-in module with paper dispenser and waste bin 32 l, matte black<br>PX40310                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Product description</b>           | <p>           VVS: 776131131<br/>           NRF: 1438628<br/>           RSK: 8920377<br/>           EAN: 5708590392219         </p>  <p>           Built-in module consisting of a paper dispenser and a 32 liter stainless steel waste container. The paper dispenser has space for approximately 500 paper napkins. The waste bin is equipped with a removable mesh basket and the solution is lockable. Including mounting kit.         </p> <p>           There is an inspection opening to indicate filling level and refilling is accessible through a lockable front flap with fall protection. Available with the same cylinder lock for both paper dispenser and waste bin.         </p> |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                |

pressalit.com