



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS grab bar, corner with vertical grip 30" x 30" x 42.9"<br>RT136108                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Color</b>                         | VVS:777568608<br>NRF:6317188<br>EAN:5708590154060<br>HMI: 25428<br>NBS:N13:436<br>FDA:ILS/D135866<br>Dark blue (RAL 5011)                                                                                                                                                                                                                                                                                                                                      |
| <b>Product description</b>           | <p>PLUS grab bars are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS grab bar combination, 1.3", reversible right/left, A:30" x B:30" x C:42.9".<br/>Material: Powder-coated aluminium and plastic.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: 440 lbs.<br>When the grab bar is loaded with 440 lbs, each wall fastener is loaded with 123 lbs.<br><i>Grab bars are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>                                                                                                                                                                                                                                  |
| <b>Materials</b>                     | Core material: Aluminium<br>Surface material: Polyester lacquer<br>Cover cap: Cyclopy plastic<br>Strap: Nylon (PA)                                                                                                                                                                                                                                                                                                                                             |
| <b>Ergonomy</b>                      | The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.                                                                                                                                                                                                                                                                                                               |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                  |



# PRESSALIT®


|                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS grab bar, corner with vertical grip 30" x 30" x 42.9"                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Item number</b> | RT136108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Cleaning</b>    | <p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningssprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b><br/>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b><br/>Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p> |



PRESSALIT®






|                    |                                                            |
|--------------------|------------------------------------------------------------|
| <b>Product</b>     | PLUS grab bar, corner with vertical grip 30" x 30" x 42.9" |
| <b>Item number</b> | RT136108                                                   |

## Mounting in different wall types

|                                                                                     |                                                                                                                                                                                                                                                                                         |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                                |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                          |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                             |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>                                                   |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8. NB!<br/>Plugs are not needed.<br/>To be ordered separately.</p>  |



# PRESSALIT®

|                                                                                     |                                                                                                                                                                                                                             |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b>                                                | PLUS grab bar, corner with vertical grip 30" x 30" x 42.9"<br>RT136108                                                                                                                                                      |                                                                                       |                                                                                     |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.           |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b><br>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                                  |  |                                                                                     |

[pressalit.com](http://pressalit.com)

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®