




<p>Product Item number</p>	<p>Pressalit SMART shower toilet, floor standing RG806000</p>
<p>Colour Product description</p>	<p>VVS:606517200 NRF:1612713 RSK:7828201 EAN:5708590398051</p>  <p>White</p> <p>Smart douchetoilets represent the next generation of bathroom comfort, combining advanced hygiene, intelligent technology, and elegant design.</p> <p>With features such as adjustable washing and drying functions, automatic lid operation, and personalized user settings, they offer a seamless and hygienic experience tailored to individual needs.</p> <p>Designed for convenience and efficiency, smart douchetoilets bring innovation and everydayluxury into modern homes.</p> <p>Pressalit SMART shower toilet, floor standing. Incl. toilet seat with cover. Incl. mounting bolts.</p>
<p>Product capacity</p>	<p>Max. 200 kg.</p>
<p>Materials Ergonomy</p>	<p>Porcelain, Urea, PP</p> <p>Personalized user settings offers a seamless and hygienic experience tailored to individual needs.</p>



PRESSALIT®

Product	Pressalit SMART shower toilet, floor standing
Item number	RG806000
Features	<ul style="list-style-type: none">• Wash and drying functions• Front and rear oscillating wash• Adjustable user preferences• Sensor for automatic open/close• Night light• Remote control included• Circular flush• Soft Close• Descaling function• Automated nozzle cleaning• Auto flush function• Suitable for both wall and floor drains• Power supply 220-240 V• Rated power 1010 W
Mains connection (V)	230
Power consumption (maximum load)	Power consumption by maximum load, watt: 1055 W Power consumption by standby: 0,06 W
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.

www.pressalit.com