




<p><b>Product</b> <b>Item number</b></p>	<p>Flexible feed and waste system 900/900 mm R2067</p>
<p><b>Product description</b></p>	<p>VVS:747477710 NRF:6132435 EAN:5708590360447</p>  <p>The flexible feed and waste systems are needed to ensure the flow of water to and from the height adjustable wash basin brackets.</p> <p>Flexible feed/waste system. For export markets. Feed pipes: 900 mm, waste pipe: 900 mm. Feed pipe, metal braid, with 3/8" coupling and 10 mm copper pipe. Flexible waste pipe, dia. 32 mm.</p>
<p><b>Materials</b></p>	<p>The feed pipes are made from SPX plastic, braided with stainless steel. The connecting nuts are 3/8" and made from brass with 10 mm copper pipe. The waste pipe is flexible, corrugated white PVC with a diameter of 32 mm. We do not recommend flushing the waste hose with formaldehyde. The elbow with removable connector is made from PP (polypropylene) with a seal of TPE (thermoplastic elastomer). Maximum temperatures of use are 80°C (continuous use) and 90°C (temporary use). PP is very resistant to water, damp and most organic solvents. The seal is made from EPDM – Temperature of use from -50°C - +120°C/150°C EPDM is particularly resistant to ozone and weather. Good resistance to heat and cold and to most chemicals – but poor resistance to petroleum products and solvents.</p>
<p><b>Ergonomy</b></p>	<p>To maximize product flexibility, it is important that the plumbing installation are correctly positioned and do not obstruct movement. The waste hose can be shortened on site to fit the installation.</p>
<p><b>Features</b></p>	<p>Pressalit supply a kit of flexible feed pipes for hot and cold water along with a flexible waste hose. The kit starts where the feed pipes attach at the isolating valves (not included) and ends where the waste kit meets the existing waste or trap in/at the wall. It assumes a connector that will fit Pressalit's Ø32 mm waste elbow. Adapters for larger connectors, e.g. Ø40 mm, must be ordered separately (not UK).</p>
<p><b>Warranty</b></p>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>



# PRESSALIT®

<b>Product</b>	Flexible feed and waste system 900/900 mm
<b>Item number</b>	R2067
<b>Cleaning</b>	<p>Flexible feed and waste systems</p> <p>When cleaning the wash basin, it is recommended that one flush the waste hose through with 50-60 degrees hot water in order to prevent build-up of soap residues inside the hose. Ensure that the hose is stretched out during this flushing.</p>

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®