



# PRESSALIT®

<b>Product</b> <b>Item number</b>	MATRIX SMALL sink without overflow R2021000
<b>Color</b>	VVS:636857000 NRF:6132502 RSK:7503000 EAN:5708590325071 HMI: 82611 NBS:N13:30,335 White
<b>Product description</b>	<p>MATRIX is a series of sinks, most of them are designed by Pressalit. MATRIX SMALL and CURVE sinks fit onto PLUS, SELECT and VALUE sink brackets, whereas MATRIX MEDIUM and ANGLE are tailor made to fit specific brackets.</p> <p>MATRIX SMALL sink, 22.6" x 17.7" x 5.1", with two integrated grab handles in the front. With tap hole diameter 1.4", without overflow. Incl. drain fitting. The sink has raised edges, preventing water from running over the back or down the outer sides. Materials: Cultured marble with a high-polished, nonporous sanitary gel coating. Compatible with sink brackets from the Pressalit PLUS and SELECT ranges.</p>
<b>Product capacity</b>	440 lbs.
<b>Materials</b>	Cultured marble with a high-polished, nonporous sanitary gel coating.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



# PRESSALIT®











<b>Product</b>	MATRIX SMALL sink without overflow
<b>Item number</b>	R2021000
<b>Cleaning</b>	<p>For cleaning the wash basin, use hot water and a mild soapy cleaning agent. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after cleaning.</p> <p>For disinfecting the wash basin, the following agents can be used:</p> <p>Sodium hydroxide 5%</p> <p>Acetic acid solution 10%</p> <p>Ethanol solution 70%</p> <p>Sodium hypochlorite 5%, active chlorine</p> <p>Sodium chloride 170g/l, diluted to 50%.</p> <p>Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after disinfection.</p> <p><b>NB! Do not use abrasive cleaning agents, as this will cause damage to the surface of the wash basin.</b></p>



PRESSALIT®







<b>Product</b>	MATRIX SMALL sink without overflow
<b>Item number</b>	R2021000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Solid Brick &gt;= Mz12</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8602 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs SX12. To be ordered separately	
	<b>Aerated Concrete P4</b> V8652 - Mounting kit, 2 lag bolts Ø10 x 100 - plugs GB14. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8602 - Mounting kit, 2 countersunk bolts Ø10 x 80, plugs SX12. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

<b>Product</b> <b>Item number</b>	MATRIX SMALL sink without overflow R2021000	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

[pressalit.com](http://pressalit.com)

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®