




<p><b>Product</b> <b>Item number</b></p>	<p>Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8922000</p>
<p><b>Color</b>  <b>Product description</b></p>	<p>EAN:5708590367187</p>  <p>White</p> <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, foldable, 31.5" x 55.1". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Materials: Molded worktop in ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. fixing kit.</p>
<p><b>Adjustability</b> <b>Adjustment height</b>  <b>Product capacity</b>  <b>Speed up</b>  <b>Noise level</b></p>	<p>Height adjustable 13,79 inch  Max load: 165 lbs.  Speed up: 0,55 inch/s Speed down: 0,55 inch/s  48 dB</p>
<p><b>Materials</b>  <b>Ergonomy</b>  <b>Features</b></p>	<p>Lifting unit: Powder-coated steel. Countertop: ABS with acrylic.</p> <p>The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.</p> <p>Easy-to-clean surfaces ensure optimum hygiene. The integrated pneumatic cylinder enables the table to be folded easily against the wall when not in use to maximize floor space.</p>



<b>Product</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable
<b>Item number</b>	R8922000
<b>Mains connection (V)</b>	120
<b>Actuator (motor)</b>	LA31 Deskline (Linak), 1500N, IPX1
<b>Control box</b>	CBD6 (Linak), IP20
<b>Wired remote control</b>	HB30 (Linak), IPX4
<b>Power consumption (maximum load)</b>	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>













# PRESSALIT®

<b>Product</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable
<b>Item number</b>	R8922000
<b>WEEE</b>	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.








<b>Product</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable
<b>Item number</b>	R8922000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	<b>Aerated Concrete P4</b> V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



<b>Product</b> <b>Item number</b>	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8922000	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	