




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Lift for worktop, electrically height adjustable RK1082
<b>Product description</b>	<p>EAN: 5708590293783 HMI: 61267</p>  <p>Pressalit INDIVO lifting units can be easily integrated into the private home, ensuring that the whole family can enjoy the full potential and use the height adjustable function. The lifting units can also help provide a flexible kitchen solution for e.g. care centers, school kitchens and school science labs, wherever there is a need for frequent height adjustments on kitchen worktops and cupboards.</p> <p>Electric lift for freestanding worktop. For worktops from 2001 - 2400 mm. Height adjustable 300 mm. Including 2 telescopic legs, brackets, longitudinal and cross braces and switch. Pressalit recommends overhang of 400 mm at either end of worktop to allow for ease of approach in wheel-chair. Please state desired length when ordering.</p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b> <b>Speed upwards</b> <b>Noise level</b>	Height adjustable 300 mm Maximum load (evenly distributed): 100 kg including worktop. Speed up mm: 20 mm/s Speed down mm: 20 mm/s 45 dB



<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1082
<b>Materials</b>	Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)
<b>Ergonomy</b>	A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen. The height of the worktop can be quickly and easily adjusted to the given user or situation. A freestanding worktop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.
<b>Features</b>	Lift heights are adjusted via switches set in the edge or directly under the worktop. Operating switches can be placed anywhere. The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users. The design of the lift makes it possible to use the worktop from all sides. Height adjustable over a range of 300 mm. Available for worktops of any length between 1400 mm and 3000 mm.
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD6 (Linak)
<b>Power consumption (maximum load)</b>	Power consumption by maximum load, watt: 300 W Power consumption by standby: 2 W
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1082
<b>Cleaning</b>	<p>INDIVO lift for kitchen worktop</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
<b>WEEE</b>	<p>Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.</p>



# PRESSALIT®

<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1082

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

## PRESSALIT®