












# PRESSALIT®

|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | PLUS fitting                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Item number</b>         | RT363035                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Colour</b>              | <p>VVS: 777569635<br/>EAN: 5708590173139<br/>NBS: N13:436</p> <p>Red (RAL 3003)</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Product description</b> |  <p>PLUS wall mounting.<br/>For wall mounting of hand rails with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Excl. mounting kit.<br/>See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS wall mounting.<br/>For wall mounting of hand rails with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Materials: Plastics.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>    | <p>Maximum load: With a span up to 1000 mm: 210 kg<br/>With a span up to 1300 mm: 150 kg.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Materials</b>           | Cover cap: Cyclopy plastic                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| <b>Warranty</b>            | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Cleaning</b>            | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |



|                    |              |
|--------------------|--------------|
| <b>Product</b>     | PLUS fitting |
| <b>Item number</b> | RT363035     |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                           |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                     |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                               |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                    |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>                                                                 |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> |  |



# PRESSALIT®

| Product<br>Item number                                                              | PLUS fitting<br>RT363035                                                                                                                                                                                       |                                                                                                                                                                                                                                                             |  |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                     |                                                                                                                                                                        |  |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®