




| | |
|--------------------------------------|--|
| Product Item number | PLUS handrail section 365 mm, incl. wall rosette and strap RT330035 |
| Colour | VVS: 777569305 EAN: 5708590146607 NBS: N13:436 Red (RAL 3003) |
| Product description | <div>  <p> RT330 - A = 365 RT331 - A = 662 RT332 - A = 790 RT333 - A = 1090 </p> </div> <p> PLUS hand rail tube, with wall rosette and strap. Length 365 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types. </p> <p> PLUS hand rail tube, with wall rosette and strap. Length 365 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Materials: Powder-coated aluminium and plastics. Excl. mounting kit. </p> |
| Product capacity | Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg. |
| Materials | Basic material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic Strap: Nylon (PA) |
| Ergonomy | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail. |
| Warranty | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. |



PRESSALIT[®]











| | |
|--------------------|--|
| Product | PLUS handrail section 365 mm, incl. wall rosette and strap |
| Item number | RT330035 |
| Cleaning | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |



PRESSALIT®











| | |
|--------------------|--|
| Product | PLUS handrail section 365 mm, incl. wall rosette and strap |
| Item number | RT330035 |

Installation in different wall types

| | | |
|---|---|---|
|  | <p>Concrete >B25</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Solid Brick >= Mz12</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Solid Sand Lime Brick >= Hlz12</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Aerated Concrete P4</p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p> |  |
|  | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> |  |



PRESSALIT®

| Product Item number | PLUS handrail section 365 mm, incl. wall rosette and strap RT330035 | | |
|---|--|---|--|
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    | |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    | |
|  | Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. |  | |

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®