




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS 90° angle handrail 154 x 154 mm with joint<br>RT350108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Colour</b>                        | VVS:777569508<br>EAN:5708590153865<br>NBS:N13:436<br><br>Dark blue (RAL 5011)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Product description</b>           | <p>PLUS corner hand rail tube, 90°, with male/female connecting joint. 154 x 154 mm, diameter 33 mm.<br/>         Requires other hand rail elements for installation. Please enquire for special hand rail solutions.<br/>         Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS corner hand rail tube, 90°, with male/female connecting joint. 154 x 154 mm, diameter 33 mm.<br/>         Requires other hand rail elements for installation. Please enquire for special hand rail solutions.<br/>         Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.<br/>         Material: Aluminium and polyester lacquer.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 1000 mm: 210 kg<br>With a span up to 1300 mm: 150 kg.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Materials</b>                     | Basic material: Aluminium<br>Surface material: Polyester lacquer                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Cleaning</b>                      | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |





# PRESSALIT®

|                    |                                                 |
|--------------------|-------------------------------------------------|
| <b>Product</b>     | PLUS 90° angle handrail 154 x 154 mm with joint |
| <b>Item number</b> | RT350108                                        |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®