




<b>Product</b> <b>Item number</b>	Pressalit Public Premium Hand dryer with sensor, brushed steel PX30515
<b>Product description</b>	<p>VVS:776133315 NRF:1438621 RSK:8865104 EAN:5708590395517</p>  <p>Stainless steel warm air hand dryer for wall mounting. Low-noise fan with sensor activated at 172mm (<math>\pm 20</math> mm). Drying time approx. 15 sec. Connection for fixed installation or installation via circuit breaker. Permanent installation must be carried out by an authorized electrician</p> <p>Power 840-1000 W. 230 V / 50/60 Hz</p>
<b>Materials</b>	European stainless steel (AISI 304)
<b>Warranty</b>	A 2-year warranty is provided for material and manufacturing defects.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.
<b>WEEE</b>	<p>Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>



PRESSALIT®

<b>Product</b>	Pressalit Public Premium Hand dryer with sensor, brushed steel
<b>Item number</b>	PX30515

---

[pressalit.com](http://pressalit.com)

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®