



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Classic Waste bin 60 l, brushed steel<br>PY30920                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Product description</b>           | VVS:777744615<br>NRF:1438611<br>RSK:8920395<br>EAN:5708590392370<br><br>Stainless steel waste bin for floor mounting or concealed wall mounting. Front panel with a stainless steel plate with rounded corners. Equipped with removable, washable polypropylene fabric bag. Capacity approx. 60 liters. Comes with mounting kit.<br><br>2.5 mm and 4 mm thick grating and mounting holes placed in the second row for concealed wall mounting. |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors.                                                                                                  |

[pressalit.com](http://pressalit.com)