




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Style Wiper, brushed steel<br>PR10600                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Product description</b>           | <p>           VVS:778406115<br/>           NRF:7001512<br/>           RSK:8663920<br/>           EAN:5708590375076<br/>           DB: 2266833         </p>  <p>           Let elegance and your personal style shine through with Pressalit Style. The long, elegant, graphic shapes will lend an exciting touch to your bathroom. Not only will your bathroom get an aesthetic makeover - it will also reflect the fact that you have made an active decision to welcome extraordinary Danish design into the décor of your home. The products are easy to fit - either with the screws included or with glue, which is purchased separately.         </p> <p>           The wiper comes with a holder and can easily be fitted on a Pressalit Style shelf or on the edge of the shower screen. Contains 1 extra wiper blade. You can purchase an extra holder and wiper blades. You can also glue the holder on the wall for easy storage.         </p> |
| <b>Materials</b>                     | Zamak, TPE and ABS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>           A 2-year warranty is provided for material and manufacturing defects.         </p> <p>           The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.         </p> <p>           Subject to changes in the product range, technical changes and printing errors.         </p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |



# PRESSALIT®

|                    |                                      |
|--------------------|--------------------------------------|
| <b>Product</b>     | Pressalit Style Wiper, brushed steel |
| <b>Item number</b> | PR10600                              |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®

24. september 2026