




<p>Product Item number</p>	<p>VALUE support arm, height adjustable R1111000</p>
<p>Colour Product description</p>	<p>VVS:615722410 NRF:6191644 RSK:7972413 EAN:5708590176437 HMI: 25414 NBS:N13:436 FDA:ILS/D135866 White</p>  <p>Support arm with leg, height adjustable 150 mm. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p> <p>Support arm with leg, height adjustable 150 mm. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p>
<p>Adjustability Adjustment height Product capacity</p>	<p>Height adjustable 150 mm Maximum load: 135 kg. When the support arm is loaded with 135 kg, each wall fastener is loaded with 29 kg.</p>
<p>Materials Ergonomy</p>	<p>The support arm is manufactured from steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion. The end caps are manufactured from nylon (PA).</p> <p>Provides firm support when you are sitting, standing, or transferring to and from a toilet.</p> <p>Good, broad support surface for the hand and arm. The rounded form gives a firm and comfortable grip.</p>













Product	VALUE support arm, height adjustable
Item number	R1111000
Features	<p>The support arm can fold up when not in use or to make more space.</p> <p>With leg for extra support.</p> <p>Height adjustable 150 mm.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% WipeClean UniversalCleaning Chlorine Disinfection Wipes Klorilli (Kilto Clean)</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>







Product	VALUE support arm, height adjustable
Item number	R1111000

Installation in different wall types

	Concrete >B25 V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.	
	Solid Brick >= Mz12 V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.	
	Aerated Concrete P4 V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.	



Product Item number	VALUE support arm, height adjustable R1111000	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (5 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (5 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	

It is the responsibility of the installer to ensure that suitable wall fasteners are used.