




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                          |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Choice Spare paper holder, brushed brass<br>Q70260                                                                                                                                                                                                                                                                                                                             |
| <b>Product description</b>           | <p>VVS: 776591205<br/>NRF: 7001079<br/>RSK: 8744116<br/>EAN: 5708590372211<br/>DB: 2173270</p>  <p>Let the Pressalit Choice bathroom accessory series elevate the décor of your bathroom and create coherence with a timeless look. You get a complete range of accessories to suit any bathroom.</p> |
| <b>Materials</b>                     | Stainless steel AISI 304, mounting knot in brass                                                                                                                                                                                                                                                                                                                                         |
| <b>Warranty</b><br><b>Cleaning</b>   | <p>A 2-year warranty is provided for material and manufacturing defects.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                    |

[pressalit.com](http://pressalit.com)