



# PRESSALIT®

|                            |                                                                                                                                                                           |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>             | PLUS shower head holder                                                                                                                                                   |
| <b>Item number</b>         | RT600000                                                                                                                                                                  |
|                            | VVS:777564700<br>NRF:6191674<br>RSK:8180966<br>EAN:5708590169965<br>HMI: 42227<br>NBS:N13:40,375                                                                          |
| <b>Color</b>               | White                                                                                                                                                                     |
| <b>Product description</b> | Shower head holder for placing on vertical grab bars.<br>Shower head holder for placing on vertical grab bars.                                                            |
| <b>Materials</b>           | Polycarbonate (PC) and ABS plastic                                                                                                                                        |
| <b>Ergonomy</b>            | Easy height adjustment with one hand or hands with little strength.                                                                                                       |
| <b>Features</b>            | For mounting on grab bars with a diameter of 1.3"                                                                                                                         |
| <b>Warranty</b>            | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                             |
| <b>Cleaning</b>            | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |

[pressalit.com](http://pressalit.com)

## PRESSALIT®