



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS fitting with strap and joint<br>RT361035                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Colour</b>                        | VVS:777569615<br>EAN:5708590146751<br>NBS:N13:436<br><br>Red (RAL 3003)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>Product description</b>           | <p>PLUS hand rail wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation.<br/> <i>Please enquire for special hand rail solutions.</i><br/>         Excl. mounting kit.<br/>         See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation.<br/> <i>Please enquire for special hand rail solutions.</i><br/>         Materials: Plastics.<br/>         Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 1000 mm: 210 kg<br>With a span up to 1300 mm: 150 kg.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Materials</b>                     | Cover cap: Cyclopy plastic<br><br>Strap: Nylon (PA)<br><br>Connecting unit: Polyphenylene oxide (PPO)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Cleaning</b>                      | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |



PRESSALIT®

|                    |                                   |
|--------------------|-----------------------------------|
| <b>Product</b>     | PLUS fitting with strap and joint |
| <b>Item number</b> | RT361035                          |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                           |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                                     |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                               |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                    |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>                                                                 |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> |  |



| Product<br>Item number                                                              | PLUS fitting with strap and joint<br>RT361035                                                                                                                                                                  |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                     |  |                                                                                     |