



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS angle grab bar section 15.8" x 6", incl. wall rosette<br>RT340108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Color</b>                         | VVS:777569408<br>EAN:5708590153834<br>NBS:N13:436<br><br>Dark blue (RAL 5011)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Product description</b>           | <p>PLUS angle grab bar tube, right, 90° angle with one wall rosette and connecting unit male joint.<br/>15.8" x 6", diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".<br/>Excl. mounting kit.<br/>See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS angle grab bar tube, right, 90° angle with one wall rosette and connecting unit male joint.<br/>15.8" x 6", diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".<br/>Materials: Powder-coated aluminium and plastics.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 39.4" : 460 lbs.<br>With a span up to 51.2" : 330 lbs.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Materials</b>                     | Core material: Aluminium<br>Surface material: Polyester lacquer<br>Cover cap: Cyclopy plastic                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>Ergonomy</b>                      | The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |



# PRESSALIT<sup>®</sup>

|                    |                                                                                                                                                                           |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>     | PLUS angle grab bar section 15.8" x 6", incl. wall rosette                                                                                                                |
| <b>Item number</b> | RT340108                                                                                                                                                                  |
| <b>Cleaning</b>    | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |



PRESSALIT®

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| <b>Product</b>     | PLUS angle grab bar section 15.8" x 6", incl. wall rosette |
| <b>Item number</b> | RT340108                                                   |

## Mounting in different wall types

|                                                                                     |                                                                                                                                                                                     |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <b>Concrete &gt;B25</b><br>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                           |    |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                                     |   |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.                                          |  |
|  | <b>Aerated Concrete P4</b><br>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.                                                |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB!<br>Plugs are not needed.<br>To be ordered separately. |  |



# PRESSALIT®

| Product<br>Item number                                                              | PLUS angle grab bar section 15.8" x 6", incl. wall rosette<br>RT340108                                                                                                                                                     |                                                                                       |                                                                                     |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.           |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.                                                                                 |  |                                                                                     |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®