




<p>Product Item number</p>	<p>PLUS 90° angle handrail 154 x 154 mm with joint RT350035</p>
<p>Colour Product description</p>	<p>VVS:777569505 EAN:5708590146720 NBS:N13:436</p>  <p>Red (RAL 3003)</p> <p>PLUS corner hand rail tube, 90°, with male/female connecting joint. 154 x 154 mm, diameter 33 mm. Requires other hand rail elements for installation. Please enquire for special hand rail solutions. Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS corner hand rail tube, 90°, with male/female connecting joint. 154 x 154 mm, diameter 33 mm. Requires other hand rail elements for installation. Please enquire for special hand rail solutions. Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Material: Aluminium and polyester lacquer.</p>
<p>Product capacity</p>	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
<p>Materials</p>	<p>Basic material: Aluminium Surface material: Polyester lacquer</p>
<p>Warranty</p>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
<p>Cleaning</p>	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>



PRESSALIT®

Product	PLUS 90° angle handrail 154 x 154 mm with joint
Item number	RT350035

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®