




|  |   |
|--|---|
| <p><b>Product</b><br/><b>Item number</b></p>             | <p>PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm<br/>RT138108</p>  |
| <p><b>Colour</b><br/><br/><b>Product description</b></p> | <p>VVS:777568708<br/>NRF:6317191<br/>EAN:5708590154077<br/>HMI: 25429<br/>NBS:N13:436<br/>FDA:ILS/D135866<br/>Dark blue (RAL 5011)</p>  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail combination, 33 mm, reversible right/left, A: 762 mm x B: 1200 mm x C: 1090 mm, for fixed mounting.<br/>The projection of 50 mm from the wall makes it easy to take hold of the rail.<br/>Inkl. wall rosette, which covers the fixings.<br/>Material: Powder-coated aluminium and plastic<br/>Excl. mounting kit.</p> |
| <p><b>Product capacity</b></p>                           | <p>Maximum load: 235 kg.<br/>When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.<br/><i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p>  |
| <p><b>Materials</b><br/><br/><b>Ergonomy</b></p>         | <p>Basic material: Aluminium<br/>Surface material: Polyester lacquer<br/>Cover cap: Cycoloy plastic<br/>Strap: Nylon (PA)</p> <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>   |
| <p><b>Warranty</b></p>                                   | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>  |













|                    |  |
|--------------------|--|
| <b>Product</b>     | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm   |
| <b>Item number</b> | RT138108   |
| <b>Cleaning</b>    | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningssprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b><br/>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b><br/>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |









|                    |  |
|--------------------|--|
| <b>Product</b>     | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm |
| <b>Item number</b> | RT138108   |

## Installation in different wall types

|   |   |   |
|---|---|---|
|    | <b>Concrete &gt;B25</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.   |    |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.   |    |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.  |  |
|  | <b>Aerated Concrete P4</b><br>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6.<br>To be ordered separately.  |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8. NB!<br>Plugs are not needed.<br>To be ordered separately. |  |



|   |  |
|---|--|
| <b>Product</b><br><b>Item number</b>  | PLUS handrail corner with vertical grip 762 x 1200 x 1090 mm<br>RT138108   |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.<br>       |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.<br> |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.<br>  |