




PRESSALIT®

Product Item number	Pressalit SMART shower toilet, wall-hung RG807000
Colour	VVS:606518300 NRF:1612714 RSK:7828202 EAN:5708590398068 White
Product description	 Smart douchetoilets represent the next generation of bathroom comfort, combining advanced hygiene, intelligent technology, and elegant design. With features such as adjustable washing and drying functions, automatic lid operation, and personalized user settings, they offer a seamless and hygienic experience tailored to individual needs. Designed for convenience and efficiency, smart douchetoilets bring innovation and everyday luxury into modern homes. Incl. toilet seat and cover. Incl. remote control (2 x AAA batteries purchased separately). Pressalit SMART shower toilet, wall-hung. Incl. toilet seat and cover. Incl. remote control (2 x AAA batteries purchased separately). Excl. mounting bolts.
Product capacity	Maximum user weight (MUM): 200 kg.
Materials	Porcelain, Urea, PP
Ergonomy	Personalized user settings offers a seamless and hygienic experience tailored to individual needs.



PRESSALIT®

Product	Pressalit SMART shower toilet, wall-hung
Item number	RG807000
Features	• Wash and drying functions • Front and rear oscillating wash • Adjustable user preferences • Sensor for automatic open/close • Heated seat • Night light • Digital information display • Remote control included • Circular flush • Soft Close • Descaling function • Automated nozzle cleaning • Power supply 220-240 V • Rated power 1055 W
Mains connection (V)	230
Power consumption (maximum load)	Power consumption by maximum load, watt: 1500 W Power consumption by standby: 0,06 W
Warranty	A 2-year warranty is provided for material and manufacturing defects.
WEEE	Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.

pressalit.com