




PRESSALIT®

Product Item number	Changing table, 31.5" x 70.9", electrically height adjustable R8943000
Color	EAN:5708590367217 White
Product description	 Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them. Changing table, freestanding, 31.5" x 70.9". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Laminate worktop, incl. 2 wire baskets. Materials: Laminate and powder-lacquered steel.
Adjustability	Height adjustable
Adjustment height	13,79 inch
Product capacity	Max load: 330 lbs.
Speed up	Speed up: 0,55 inch/s Speed down: 0,55 inch/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-coated steel. Countertop: Melamine.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene.
Mains connection (V)	120



Product	Changing table, 31.5" x 70.9", electrically height adjustable
Item number	R8943000
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättspnit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
Declaration of conformity	This product is solely intended for the US and Canada, and has no EU declaration of conformity.



PRESSALIT®

Product	Changing table, 31.5" x 70.9", electrically height adjustable
Item number	R8943000

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®