



PRESSALIT®

Product Item number	Dual flush button for PLUS fold down grab bar R9342
Product description	<p>VVS:615859300 NRF:6190666 EAN:5708590314686 NBS:N13:436</p> <p>Flush button can be used with PLUS fold down grab bars and SELECT TL2 toilet lifter.</p> <p>Flush button, battery operated (2 x 1½ Volt AAA), for mounting to underside of PLUS support arm.</p> <p>Interconnection with SELECT toilet lifter can be handled by Pressalit. In that case, R9343 (battery) or R9344 (mains) must be added to the order.</p> <p>The flush button also works with selected cisterns from Geberit, please note that further Geberit parts are required.</p>
Materials Features	<p>PA</p> <p>The flush button for attachment to PLUS fold down grab bars comes with 2 buttons:</p> <p>Combination blue/green: Blue button = big flush (lots of water) Green button = small flush (not so much water).</p> <p>Combination blue/black: Blue button = big flush (lots of water) Black button = small flush (not so much water).</p> <p>Combination black/green: Black button = big flush (lots of water) Green button = small flush (not so much water).</p> <p>Combination red/black: Red button = big flush (lots of water) Black button = small flush (not so much water).</p>
Warranty WEEE	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> <p>Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.</p>



PRESSALIT®

Product	Dual flush button for PLUS fold down grab bar
Item number	R9342

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®