













PRESSALIT®

Product Item number	VALUE distance piece R1201000
Colour	VVS:636859920 NRF:6132432 EAN:5708590369075 White
Product description	 VALUE distance piece can be used where extra space below the wash basin is needed VALUE distance piece for wash basin, 600 x 100 x 100 mm. Incl. fixing bolts for wash basin. Fits MATRIX SMALL and CURVE/CURVE II wash basins. Excl. wall fixing kit.
Product capacity	Maximum load: 70 kg. Suitable for wash basins weighing no more than 22 kg. When the wash basin is loaded with 70 kg, each wall fastener will be carrying 187 kg. <i>Wash basin brackets need to be able to carry the weight of the wash basin, as well as support the weight of the person who is leaning against the wash basin or who is using the wash basin to rise from seated position.</i> Neither wash basin nor wash basin bracket are intended to carry the full body weight of a person, and the test methods applicable to wash basin brackets reflect this: ISO 17966 prescribes a static test on the front edge of the wash basin at 75% of maximum user weight, i.e. when the maximum load on a wash basin bracket is given as 70 kg and the wash basin weighs 22 kg, it is – according to ISO 17966 – the equivalent of a user weighing 64 kg leaning on the front edge of the wash basin.
Materials	Steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion






Product	VALUE distance piece
Item number	R1201000

Installation in different wall types

	Concrete >B25 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Solid Brick >= Mz12 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers. To be ordered separately.	
	Aerated Concrete P4 V8655 - Mounting kit, 4 coach screws Ø10 x 70, plugs GB14, with grey screw covers. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with white screw covers. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	VALUE distance piece R1201000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®