



# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | PLUS end piece with strap<br>RT362108                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Colour</b>                        | VVS:777569628<br>EAN:5708590153896<br>NBS:N13:436<br><br>Dark blue (RAL 5011)<br><br>                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Product description</b>           | <p>PLUS end piece with tube connector, horizontal/vertical, with connecting unit male joint.<br/>For assembling tubes with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i></p> <p>PLUS end piece with tube connector, horizontal/vertical, with connecting unit male joint.<br/>For assembling tubes with diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Materials: Plastics.</p> |
| <b>Product capacity</b>              | Maximum load: With a span up to 1000 mm: 210 kg<br>With a span up to 1300 mm: 150 kg.                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Materials</b>                     | Cover cap: Cyclopy plastic<br><br>Strap: Nylon (PA)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>Cleaning</b>                      | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.                                                                                                                                                                                                                                                                                                                                                                                   |



# PRESSALIT®

|                    |                           |
|--------------------|---------------------------|
| <b>Product</b>     | PLUS end piece with strap |
| <b>Item number</b> | RT362108                  |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®