




PRESSALIT®

Product Item number	MATRIX ANGLE DEEP wash basin without overflow, left-facing R2143112000
Colour	VVS: 639871000 EAN: 5708590340845 HMI: 138168 White 
Product description	MATRIX is a series of wash basins, most of them are designed by Pressalit. MATRIX SMALL and CURVE wash basins fit onto PLUS, SELECT and VALUE wash basin brackets, whereas MATRIX MEDIUM, ANGLE, ANGLE DEEP and SQUARE are tailor made to fit specific brackets. MATRIX ANGLE DEEP vanity wash basin, 1000 x 571 x 158 mm, left-facing, with two integrated anthracite handrails in the front, with tap hole Ø36 mm, without overflow. Supplied with drain fitting. The wash basin has raised edges, preventing water from running over the back or down the outer sides. Materials: Cultured marble with a high-polished, pore-free sanitary gel coating. Suitable for mounting on MATRIX basin unit (R4842 (UK R4847), R2011).
Product capacity	200 kg.
Materials	Cultured marble with a high-polished, pore-free sanitary gel coating.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT®

Product	MATRIX ANGLE DEEP wash basin without overflow, left-facing
Item number	R2143112000
Cleaning	Wash basin For cleaning the wash basin, use hot water and a mild soapy cleaning agent. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after cleaning. For disinfecting the wash basin, the following agents can be used: Sodium hydroxide 5% Acetic acid solution 10% Ethanol solution 70% Sodium hypochlorite 5%, active chlorine Sodium chloride 170g/l, diluted to 50%. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after disinfection. NB! Do not use abrasive cleaning agents, as this will cause damage to the surface of the wash basin.

pressalit.com

PRESSALIT®