




| | |
|--|---|
| <p>Product Item number</p> | <p>VALUE II support arm, fixed height R1109000</p> |
| <p>Colour Product description</p> | <p>VVS:615891100 NRF:6191057 RSK:8487434 EAN:5708590367576 HMI: 123560 FDA:ILS/D135866</p> <p>White</p>  <p>VALUE II support arm, fixed, foldable, projection 850 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p> <p>VALUE II support arm, fixed, foldable, projection 850 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Materials: Rilsan-coated steel, pressure-cast aluminium, plastic. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p> |
| <p>Adjustability Product capacity</p> | <p>Fixed mounting</p> <p>Maximum load: 120 kg. When the support arm is loaded with 120 kg, each wall fastener is loaded with 145 kg.</p> |
| <p>Materials Ergonomy Features</p> | <p>The support arm is manufactured from steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion.</p> <p>Provides firm support when you are sitting, standing, or transferring to and from a toilet.</p> <p>Good, broad support surface for the hand and arm. The ergonomic form gives a firm and comfortable grip.</p> <p>The support arm can fold up when not in use or to make more space.</p> |
| <p>Warranty</p> | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> |












| | |
|--------------------|---|
| Product | VALUE II support arm, fixed height |
| Item number | R1109000 |
| Cleaning | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% WipeClean UniversalCleaning Chlorine Disinfection Wipes Klorilli (Kilto Clean)</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> |







| | |
|--------------------|------------------------------------|
| Product | VALUE II support arm, fixed height |
| Item number | R1109000 |

Installation in different wall types

| | | |
|---|--|---|
|  | Concrete >B25 V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately. |  |
|  | Solid Brick >= Mz12 V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately. |  |
|  | Solid Sand Lime Brick >= Hlz12 V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately. |  |
|  | Aerated Concrete P4 V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately. |  |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8593 - 4 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately. |  |



| Product Item number | VALUE II support arm, fixed height R1109000 | |
|---|--|---|
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |  |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |  |
|  | Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. |  |

Bolts for wall fixing are included. It is the responsibility of the installer to ensure that suitable plugs are used. Please see mounting instruction.