



# PRESSALIT®

<b>Product</b> <b>Item number</b>	Lift for countertop, electrically height adjustable RK1081-93
<b>Product description</b>	<p>EAN:5708590301365</p> <p>Pressalit INDIVO lifting units can be easily integrated into the private home, ensuring that the whole family can enjoy the full potential and use the height adjustable function. The lifting units can also help provide a flexible kitchen solution for e.g. care centers, school kitchens and school science labs, wherever there is a need for frequent height adjustments on kitchen countertops and wall cabinets.</p> <p>Electric lift for freestanding countertop. For countertops from 55.1" - 78.7" . Height adjustable 11.8". Including 2 telescopic legs, longitudinal and cross braces and switch. Pressalit recommends overhang of 7.9" at either end to allow ease of approach in wheel-chair. Please state desired length when ordering.</p>
<b>Adjustability</b>	Height adjustable
<b>Adjustment height</b>	11,82 inch
<b>Product capacity</b>	Maximum load (evenly distributed): 220 lbs including countertop.
<b>Speed up</b>	Speed up: 0,79 inch/s Speed down: 0,79 inch/s
<b>Noise level</b>	45 dB



<b>Product</b>	Lift for countertop, electrically height adjustable
<b>Item number</b>	RK1081-93
<b>Materials</b>	<p>Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p>
<b>Ergonomy</b>	<p>A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen. The height of the countertop can be quickly and easily adjusted to the given user or situation. A freestanding countertop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.</p>
<b>Features</b>	<p>Lift heights are adjusted via switches set in the edge or directly under the countertop. Operating switches can be placed anywhere. The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users. The design of the lift makes it possible to use the countertop from all sides. Height adjustable over a range of 11.8". Available for countertops of any length between 55.1" and 11.8".</p>
<b>Mains connection (V)</b>	120
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD4 (Linak) IP22
<b>Power consumption (maximum load)</b>	<p>Power consumption by maximum load: 300 W Power consumption by standby: 2 W</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



# PRESSALIT®

<b>Product</b>	Lift for countertop, electrically height adjustable
<b>Item number</b>	RK1081-93
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>



# PRESSALIT®

<b>Product</b>	Lift for countertop, electrically height adjustable
<b>Item number</b>	RK1081-93

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

## PRESSALIT®