




# PRESSALIT®

|                                      |                                                                                                                                                                                                                                                                                                                                                |                                                                                     |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b> | Pressalit Public Premium Toilet paper holder with space for 5 rolls of toilet paper, matte black<br>PX40220                                                                                                                                                                                                                                    |                                                                                     |
| <b>Product description</b>           | VVS: 776130531<br>NRF: 1438653<br>RSK: 8920375<br>EAN: 5708590392707                                                                                                                                                                                                                                                                           |  |
| <b>Materials</b>                     | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                            |                                                                                     |
| <b>Warranty</b><br><b>Cleaning</b>   | A 2-year warranty is provided for material and manufacturing defects.<br><br>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.<br><br>Subject to changes in the product range, technical changes and printing errors. |                                                                                     |

[pressalit.com](http://pressalit.com)