



PRESSALIT®

Product Item number	Pressalit Public Premium Infrared sensor module for dispensers PX00799
Product description	VVS: 774565999 NRF: 1438623 RSK: 8920357 EAN: 5708590392066 Infrared sensor with pump for use in soap dispensers. The sensor reacts to light differences. Detection distance approx. 5 cm. Fits soap dispensers PX10320, PX30320, PX40320, PY10715, PY20725 and PY30735. 3V. Requires 2 LR14 batteries (not included).
Warranty Cleaning	A 2-year warranty is provided for material and manufacturing defects. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. Subject to changes in the product range, technical changes and printing errors.

pressalit.com