




|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product Item number</b> | Pressalit Public Classic Paper dispenser, manual, 500 sheets, brushed steel<br>PY30110                                                                                                                                                                                                                                                                                                                                                                                    |
| <b>Product description</b> | <p>VVS:776135515<br/>NRF:1438631<br/>RSK:8920387<br/>EAN:5708590392318</p>  <p>Stainless steel paper dispenser for wall mounting. For approx. 500 paper napkins. Key-operated opening. Incl. mounting kit.</p> <p>Stainless steel housing. Fills at the top and has an inspection opening to indicate fill level.</p> <p>Recommended paper size (folded): 240-250 mm x 100-115 mm.</p> |
| <b>Materials</b>           | European stainless steel (AISI 304)                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Warranty</b>            | A 2-year warranty is provided for material and manufacturing defects.                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Cleaning</b>            | <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>                                                                                                                                                                                                  |