



Product	PLUS grab bar section 29.4", incl. wall rosette
Item number	RT322112
Color	<p>VVS:777569222 NRF:6311257 EAN:5708590318875 NBS:N13:436</p> <p>Anthracite gray</p>
Product description	<p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 29.4", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 29.4", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
Product capacity	<p>Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.</p>
Materials	<p>Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cycoloy plastic</p>
Ergonomy	<p>The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>



PRESSALIT®

Product	PLUS grab bar section 29.4", incl. wall rosette
Item number	RT322112








Product	PLUS grab bar section 29.4", incl. wall rosette
Item number	RT322112

Mounting in different wall types

	<p>Concrete >B25 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Brick >= Mz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



Product Item number	PLUS grab bar section 29.4", incl. wall rosette RT322112
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 