




Product Item number	PLUS handrail section 1046 mm, incl. wall rosette RT323112
Colour	<p>VVS:777569232 NRF:6311259 EAN:5708590318882 NBS:N13:436</p> <p>Anthracite grey</p> 
Product description	<p>PLUS hand rail tube, with wall rosette and connecting unit female joint. Length 1046 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail tube, with wall rosette and connecting unit female joint. Length 1046 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
Product capacity	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
Materials	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cyclopy plastic</p>
Ergonomy	<p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>



PRESSALIT®











Product	PLUS handrail section 1046 mm, incl. wall rosette
Item number	RT323112
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









Product	PLUS handrail section 1046 mm, incl. wall rosette
Item number	RT323112

Installation in different wall types

	Concrete >B25 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Brick >= Mz12 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	PLUS handrail section 1046 mm, incl. wall rosette RT323112		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®