













|                            |  |
|----------------------------|--|
| <b>Product</b>             | PLUS fitting with strap  |
| <b>Item number</b>         | RT360108   |
|                            | VVS:777569608<br>EAN:5708590153872<br>NBS:N13:436  |
| <b>Color</b>               | Dark blue (RAL 5011)   |
| <b>Product description</b> | <p>PLUS grab bar wall mounting with strap.<br/>For assembling tubes with diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Excl. mounting kit.<br/>See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar wall mounting with strap.<br/>For assembling tubes with diameter 1.3".<br/>Requires other grab bar elements for installation.<br/><i>Please enquire for special grab bar solutions.</i><br/>Materials: Plastics.<br/>Excl. mounting kit.</p> |
| <b>Product capacity</b>    | Maximum load: With a span up to 39.4" : 460 lbs.<br>With a span up to 51.2" : 330 lbs.   |
| <b>Materials</b>           | Cover cap: Cycloy plastic<br>Strap: Nylon (PA)   |
| <b>Warranty</b>            | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.  |
| <b>Cleaning</b>            | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.  |









|                    |                         |
|--------------------|-------------------------|
| <b>Product</b>     | PLUS fitting with strap |
| <b>Item number</b> | RT360108                |

## Mounting in different wall types

|   |  |   |
|---|--|---|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>   |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>   |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>  |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>  |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB!<br/>Plugs are not needed.<br/>To be ordered separately.</p> |  |



| <b>Product</b><br><b>Item number</b>  | <b>PLUS fitting with strap</b><br><b>RT360108</b>  |   |
|---|--|---|
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.</p>           |    |
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.</p> |    |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>  |  |